


DR10-F



Ordering dimensions in **blue**

Surface roughness	R_{tmax}	R_a
Sliding surface	$\leq 2 \mu m$	0,05–0,3 μm
Bottom of groove	$\leq 6,3 \mu m$	$\leq 1,6 \mu m$
Groove face	$\leq 15 \mu m$	$\leq 3 \mu m$

Hardness: On the surface min 55 HRC, hardened depth > 0,3 mm.
Bearing area: 50–95% and a cutting depth of 0,5 R_z based on $C_{ref} = 0\%$

Standard dimensions					Maximal radial extrusion gap		
D	d	L	R	$s^{1)}$			
H8	incl.	h8	+ 0,2		100 bar	200 bar	350 bar
mm					mm		
10	19	D – 4,9	2,2	0,3	0,15	0,10	0,10
19	38	D – 7,5	3,2	0,5	0,20	0,15	0,10
38	200	D – 11	4,2	0,7	0,25	0,20	0,10

¹⁾ Extrusion gap values shown above are valid for a temperature of 80 °C, higher temperatures require lower values.

Ordering example

Profile
D x d x L [mm]
Sealing material / Energizer

Rotary seal DR10-F
100 x 89 x 4,2
SKF Ecoptfe / NBR70

DR10-F

Operating parameters

Material Seal	Energiizer	Temperature		Speed ¹⁾	Pressure ²⁾
		from	to	max	max
–		°C		m/s	bar (MPa)
■ SKF Eoptfe	FPM75	–20	+200	0,4	350 (35)
■ SKF Eoptfe	NBR70	–30	+100	0,4	350 (35)

IMPORTANT NOTE: The stated operating conditions represent general indications. It is recommended not to use all maximum values simultaneously.

¹⁾ Surface speed limit values are valid only in the presence of a lubrication film.

²⁾ Pressure ratings depend on the size of the extrusion gap.